FGSB-MSHS-M10



FiberGuide® Horizontal Straight Section, 4x18 in, 10ft Long, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Straight section
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Straight section

Dimensions

Length	3048 mm 120 in
System Dimensions	102 mm x 457 mm (4 in x 18 in)

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net	13.485 kg	29.729 lb
in orgina, mot	10.100 kg	22.72210

Regulatory Compliance/Certifications

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 7, 2025



FGSB-MSHS-M10

ROHS

CHINA-ROHS

REACH-SVHC

Classification

Below maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant





©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 7, 2025

