

MC-KD8M-9-96



Heavy Duty Double T-Arm Monopole Mount Kit, Includes (2) Ring Mounts for 15"-50" OD Monopole, 8 ft x 3-1/2" OD face pipes, and (9) 96" x 2-7/8" OD Antenna Pipes.

Heavy Duty Double T-Arm mount design with extended 69" Stand-off for Monopole/Monopine applications featuring sturdy corner tie-backs for added stability.

Product Classification

Product Type Monopole T-frame kit

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity 9
Sectors, quantity 3

Dimensions

Face Width 2.438 m | 8 ft
Width 2,438.4 mm | 96 in
Pipe Length 2,438.4 mm | 96 in
Mounting Diameter, maximum 1270 mm | 50 in
Mounting Diameter, minimum 381 mm | 15 in
Stand-off Distance 1,752.6 mm | 69 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative
Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

MC-KD8M-9-96

Included	Plain end pipes (9) Ring mounts (2) Stand-off arms
Packaging quantity	1
Weight, net	948.462 kg 2091 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--