

F137CCB5



FlexTwist® Flexible Twist for WR137, 6.425–7.125 GHz, with interface types CPR137G and CPR137G, 1200 mm

Product Classification

| | |
|----------------------|---------------------------------------|
| Product Type | Rectangular waveguide, flexible twist |
| Product Brand | FlexTwist® |

General Specifications

| | |
|--------------------|----------------|
| Component | Flexible Twist |
| Interface | CPR137G |
| Interface 2 | CPR137G |

Dimensions

| | |
|-----------------------|---------------------|
| Length | 1200 mm 47.244 in |
| Waveguide Size | WR137 WG14 R70 |

Electrical Specifications

| | |
|---------------------------------|------------------------|
| Attenuation | 0.3 dB/m 0.091 dB/ft |
| Average Power | 2000 W |
| Operating Frequency Band | 6.425 – 7.125 GHz |
| Peak Power | 500 kW |
| VSWR | 1.05 |

Mechanical Specifications

| | |
|--|----------------------------------|
| Minimum Bend Radius, Multiple Bends (E Plane) | 102 mm 4.016 in |
| Minimum Bend Radius, Multiple Bends (H Plane) | 204 mm 8.031 in |
| Maximum Twist | 214 °/m 65.227 °/ft |
| Pressurization, maximum | 0.207 N/mm ² 30 psi |

F137CCB5

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

