

F137HHB2



FlexTwist® Flexible Twist for WR137, 6.425–7.125 GHz, with interface types PDR70 and PDR70, 600 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PDR70
Interface 2	PDR70

Dimensions

Length	600 mm 23.622 in
Waveguide Size	WR137 WG14 R70

Electrical Specifications

Attenuation	0.3 dB/m 0.091 dB/ft
Average Power	2000 W
Operating Frequency Band	6.425 – 7.125 GHz
Peak Power	500 kW
VSWR	1.03

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	102 mm 4.016 in
Minimum Bend Radius, Multiple Bends (H Plane)	204 mm 8.031 in
Maximum Twist	214 °/m 65.227 °/ft
Pressurization, maximum	0.207 N/mm ² 30 psi

F137HHB2

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system