


CX3350009 | 125T135P3625JCASS COEX



ConQuest® Cable in Conduit, 1 1/4 in, SDR 13.5, terracotta (P3® 625 JCASS)

Product Classification

Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	625 Series

General Specifications

Cable Type	625 series
Cable-In-Conduit Type	P3® in duct
Color	Terracotta
Conduit Type	Non-toneable
Wall Type	Smooth

Dimensions

Length	731.52 m 2400 ft
Wall Thickness Designation	SDR 13.5
Nominal Size	1-1/4 in

Packaging and Weights

Weight, net	608.659 kg/km 409 lb/kft
-------------	----------------------------

Included Products

530101403 P3® 625 JCASS SM MT	-	75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
5308103 P3® 625 JCASS	-	75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
CX3399999 125T135 EMPTY DUCT COEX	-	ConQuest® Empty Conduit, 1 1/4 in, SDR 13.5, terracotta

