

A-100880



Meter Cabinet with Backboard Only

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

General Specifications

Access Front door

Accessories Cable plate | In-ground root | Plinth

Batteries Supported 0

Batteries Supported, with optional battery pedestal 0

Cabinet Type Meter cabinet

Color Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

Door Security 7 mm triangle lock

Internal Mounting Surface 12 mm plywood backboard

Dimensions

Height 1016 mm | 40 in

Width 660.4 mm | 26 in

Depth 254 mm | 10 in

Depth, without door 254 mm | 10 in

Electrical Specifications

ac Feeds, Outgoing, quantity 0

Generator Connection No connection

Material Specifications

Finish Powder coated

A-100880

Material Type Galvanized steel

Packaging and Weights

Weight, net 35.834 kg | 79 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

