FMT-GQR085A00-A72B



FMT Fiber Termination Panel, with sliding tray, 72 LC/UPC, singlemode, 2RU, 19 in, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FMT

General Specifications

Functionality Patching

Body Style Symmetrical

Color Black
Interface, front LC/UPC

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

Shelf Movement Sliding

Total Ports, quantity 72

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 279.91 mm | 11.02 in

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

COMMSC PE®

FMT-GQR085A00-A72B

Packaging and Weights

Included Mounting hardware

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

