# FMT-GRT070A00-A72B



FMT Fiber Termination Panel, with sliding tray, 72 SC/UPC, singlemode, 2RU, 19 in, putty white

### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FMT

### General Specifications

**Functionality** Patching

Body Style Symmetrical

ColorBlackColor, frontBlackInterface, frontSC

Interface Feature, front Standard

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

**Shelf Movement** Sliding

Total Ports, quantity 72

#### Dimensions

 Height
 88.9 mm | 3.5 in


 Width
 482.6 mm | 19 in

 Depth
 279.91 mm | 11.02 in

### Ordering Tree



# FMT-GRT070A00-A72B



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

### Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

