FMT-GTL0J0U20-A48P



FMT Fiber Termination/Splice Panel, with sliding tray, 48 SC/APC, singlemode, 2RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FMT

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Color	Black + Putty white (front)
Interface, front	SC/APC
Rack Type	EIA 19 in EIA 23 in
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	48
Dimensions	
Height	88.9 mm 3.5 in

Width	482.6 mm 19 in
Depth	279.91 mm 11.02 in


Ordering Tree

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



FMT-GTL0J0U20-A48P



Α	Adapter-only	-
С	Multimode stranded pigtails (OM 3/4)	
U	Singlemode stranded pigtails	
R	Singlemode ribbon pigtails	

Material Specifications

Finish	Powder coated
	· on abi obatoa

Material Type

Steel

Optical Specifications

Fiber Mode

Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

