

FPS-MPP4AJJ

OMX Singlemode Splitter Module, 1 x 32, SC/APC, symmetrical split ratio

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

OBSOLETE

This product was discontinued on: December 30, 2018

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter module
Product Brand	OMX600®
Product Series	OMX

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Access	Front
Application	For use with OMX frames
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Interface, rear	SC/APC
Module Color	Putty white
Split Ratio	Symmetrical
Splitter, quantity	1

Optical Specifications

FPS-MPP4AJJ

Directivity, minimum	60 dB
Insertion Loss, Splitter, maximum	16.7 dB

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant

