FPX-12MPLS07



FPX Fiber Optic MPO Module, Singlemode OS2, 12 fiber SC/UPC adapter, left, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a "grow as you go" approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	FPX

General Specifications

Functionality	Breakout	
Application	For use with FPX panels	
Adapter Color	Blue	
Adapters, quantity, front	12	
Adapters, quantity, rear	1	
Body Style	Left orientation Simplex	
Color, front	Putty white	
Color, housing	Putty white	
Color, rear	Putty white	
Interface, front	SC/UPC	
Interface, rear	MPO	
Interface Feature, rear	Standard	
Polarity	Pairs, straight	
Total Ports, quantity, front	12	
Dimensions		
Height	33.02 mm 1.3 in	

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024



FPX-12MPLS07


Width

176.53 mm | 6.95 in

Depth

127 mm | 5 in

Ordering Tree



² LC only

Optical Specifications

Fiber Mode	Singlemode		
Fiber Type	0S2		

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	1	
Packaging Type	Bag	Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024



FPX-12MPLS07

ROHS

TL 9000:2016 (R6)

UK-ROHS

Compliant

Compliant to this quality management practice

Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

