## RDT-SM12J00D1529A



# RapidFiber® Mini-RDT Distribution Terminal, 12-fiber, SC/APC, Indoor /outdoor cable, 500 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution terminal

Product Brand RapidFiber®

Product Series Mini-RDT

#### General Specifications

Adapters, quantity 12

 Cable Entry Location
 Bottom left | Bottom right

 Cable Type
 Indoor/outdoor - Stranded

Color Gray
Interface SC/APC
Interface, stub MPO
Mounting Wall
Port, quantity 12

#### Dimensions

 Height
 200 mm | 7.874 in

 Width
 140 mm | 5.512 in

 Depth
 60 mm | 2.362 in


 Cable Length
 152.4 m | 500 ft

 Outer Cable Diameter
 4 mm | 0.157 in


#### Dimension Drawing



## RDT-SM12J00D1529A



### Ordering Tree



## RDT-SM12J00D1529A

### Material Specifications

Material Type Plastic

**Optical Specifications** 

Fiber Mode Singlemode

**Environmental Specifications** 

Environmental Space Indoor

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

