309070-000 | FIST-GPS2-J-NNN-0



FIST-GPS2 Fiber Panel for holding up to 4 GPST Patch/Splice Trays, unloaded, 2RU, 19 in, gray

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Brand FIST®

Product Series FIST-GPS2

General Specifications

Functionality Patching | Splicing

Application Used in FIST-GR3-style frames only

Color Gray
Color, front Gray

Growth Configuration Unloaded Interface, front Unloaded

Rack Type EIA 19 in | ETSI 600 mm

Rack Units 2

Shelf Movement Sliding

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

Material Specifications

Finish Powder coated

Material Type Galvanized steel

COMMSC PE°

309070-000 | FIST-GPS2-J-NNN-0

Environmental Specifications

Operating Temperature -5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

