

FIST-SODF2-Fiber Termination/Splice Block, pre-terminated with pigtails, 24 SC/APC, singlemode, gray

OBSOLETE

This product was discontinued on: March 1, 2018

## Product Classification

Regional Availability	EMEA
Product Type	Fiber patch/splice block
Product Brand	FIST®
Product Series	FIST-SODF2

## General Specifications

Functionality	Patching   Splicing
Application	Used in FIST-SODF-style frames only
Color	Gray
Color, front	Gray
Interface, front	SC/APC
Total Ports, quantity	24

## Optical Specifications

Fiber Mode	Singlemode
------------	------------

## Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing

## Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

