

FD3-AB096J00JJBP1



Enhanced Mini FDH 3000 Fiber Distribution Hub, 96-fiber shell, 96 fibers loaded, SC/APC, distribution patch, feeder stub

Product Classification

| | |
|------------------------------|------------------------|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |

General Specifications

| | |
|--|-------------------------|
| Access | Front |
| Cable Type | Dielectric - Loose Tube |
| Color | Putty white |
| Distribution Cables, quantity | 2 |
| Distribution Ports, quantity | 96 |
| Fibers per Distribution Cable, quantity | 48 |
| Fibers per Feeder Cable, quantity | 12 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pole Wall |
| Splitter Slots, quantity | 8 |

Dimensions

| | |
|-----------------------|------------------|
| Height | 584.2 mm 23 in |
| Width | 330.2 mm 13 in |
| Depth | 203.2 mm 8 in |
| Cable Length | 30.48 m 100 ft |
| Enclosure Size | Mini |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Aluminum |

FD3-AB096J00JJBP1

Environmental Specifications

| | |
|--------------------------------|---|
| Environmental Space | Aerial |
| Qualification Standards | Telcordia GR-3123-CORE Telcordia GR-3125-CORE |

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Pallet |