

# FDT-CK048NXV0250

---



iFDT Indoor Fiber Distribution Terminal, 48-fiber, LC/UPC, loose tube IFC cable, 250 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Series</b>	IFDT

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Adapters, quantity</b>	24
<b>Cable Entry Location</b>	Bottom right   Top right
<b>Cable Type</b>	IFC - Stranded
<b>Color</b>	Putty white
<b>Front Door Type</b>	Double hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface</b>	LC/UPC
<b>Lock Type</b>	Padlock ready
<b>Mounting</b>	Wall
<b>Port, quantity</b>	48

## Dimensions

<b>Height</b>	476.25 mm   18.75 in
<b>Width</b>	368.3 mm   14.5 in
<b>Depth</b>	127 mm   5 in
<b>Cable Length</b>	76.2 m   250 ft

## Ordering Tree

# FDT-CK048NXV0250



## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Environmental Space** Indoor

**Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

## Packaging and Weights

**Packaging quantity** 1

# FDT-CK048NXV0250

---

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

