NG4-MMDTMOROOO



NG4access® MPO Module, multimode, SC/UPC-MPO 12 fiber, right exit (for MPO module)

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability Latin America | North America

Product Type Fiber module

Product Brand NG4access®

Product Series NG4

General Specifications

Functionality Breakout

Application NG4 MPO module

Adapter Color Aqua
Adapters, quantity, front 12

Body Style Simplex
Color, front Black
Color, housing Black
Color, rear Black
Interface, front SC/UPC
Interface, rear MPO

Polarity Method A

Total Fibers, quantity 12

Total Ports, quantity, front 12

Dimensions

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 130.3 mm | 5.13 in

COMMSCOPE®

NG4-MMDTMOROOO

Outline Drawing



Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, bend insensitive

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+40 \,^{\circ}\text{C}$ ($+23 \,^{\circ}\text{F}$ to $+104 \,^{\circ}\text{F}$)

Storage Temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ ($+23 \,^{\circ}\text{F}$ to $+122 \,^{\circ}\text{F}$)

Relative Humidity Up to 85%, non-condensing

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

Page 2 of 3



NG4-MMDTMOROOO

UK-ROHS

Compliant



COMMSCOPE®

Page 3 of 3