

# NG4-VMKNLF4H010GM



NG4access® Module VAM, Monitoring, 70/30, multimode, LC/UPC, front, left, 4 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Monitoring module
Product Brand	NG4access®
Product Series	NG4

## General Specifications

Device Type	Plug-and-play module
Functionality	Splitting
Access	Front
Application	For use with NG4 access frames
Circuits, quantity	4
Distribution Type	1 x 2 splitter
Interface, front	LC/UPC
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Split Ratio	70/30
Splitter, quantity	4
Tray Orientation	Left orientation

## Dimensions

Height	13.21 mm   0.52 in
Width	159.77 mm   6.29 in
Depth	130.3 mm   5.13 in

# NG4-VMKNLF4H010GM

---

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

