



SYSTIMAX 360™ GigaSPEED X10D® and GigaSPEED XL® Evolve Angled 2U U/UTP Panel Kit

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	GigaSPEED X10D® SYSTIMAX 360™

General Specifications

Cable Type	Unshielded
Color	Cool gray Satin chrome
Intelligence Type	iPatch® ready
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	48
Wiring	T568A T568B

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth, with cable management	266.7 mm 10.5 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

760152793 | 360-A-E-KIT-2U

Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
Weight, net	1.497 kg 3.3 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

