

## SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Patch Panel, 24 port



### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

SYSTIMAX®

**Product Type**

RJ45 patch panel

**Product Brand**

SYSTIMAX 360™ | iPatch®

### General Specifications

**ANSI/TIA Category**

6A

**Cable Type**

Unshielded

**Color**

Silver

**Intelligence Type**

iPatch® enabled

**Panel Style**

Straight

**Rack Units**

1

**Total Ports, quantity**

24

**Wiring**

T568A | T568B

### Dimensions

**Height**

44.45 mm | 1.75 in

**Width**

482.6 mm | 19 in

**Depth**

206.5 mm | 8.13 in

**Compatible Diameter Over Dielectric, maximum**

1.168 mm | 0.046 in

### Electrical Specifications

**Current Rating at Temperature**

1.5 A @ 20 °C | 1.5 A @ 68 °F

**Dielectric Withstand Voltage, RMS, conductive surface**

1,500 Vac @ 60 Hz

**Insulation Resistance, minimum**

500 MOhm

# 760201145 | 360-iP-1100-E-GS6-1U-24

---

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

