

FD3-AE216J1AGDBP1



FDH 3000 Small Fiber Distribution Cabinet, 216F, SC/APC, 32-splitter module, single armor loose tube, 100 ft, 12F

Product Classification

| | |
|------------------------------|------------------------|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |

General Specifications

| | |
|--|-----------------------------|
| Access | Front |
| Cable Type | Armored - Single Loose Tube |
| Color | Putty white |
| Distribution Cables, quantity | 2 |
| Distribution Ports, quantity | 288 |
| Fibers per Feeder Cable, quantity | 12 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pad |
| Split Ratio | Symmetrical |
| Splitter Slots, quantity | 12 |
| Splitter Type | 1 x 32 |
| Splitter, quantity | 1 |

Dimensions

| | |
|-----------------------|--------------------|
| Height | 914 mm 35.984 in |
| Width | 686 mm 27.008 in |
| Depth | 457 mm 17.992 in |
| Cable Length | 30.48 m 100 ft |
| Enclosure Size | Small |

Material Specifications

FD3-AE216J1AGDBP1

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Environmental Specifications

| | |
|----------------------------|--------------|
| Environmental Space | Above ground |
|----------------------------|--------------|

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Pallet |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

