

# FD3-AE288J00U20P2



FDH 3000 Small Fiber Distribution In-Hub Splice Cabinet, 288F, SC/APC,  $\emptyset$  spltr./stub, LT pigtails, heat-shrink fusion, 24F

## Product Classification

|                              |                        |
|------------------------------|------------------------|
| <b>Regional Availability</b> | North America          |
| <b>Product Type</b>          | Fiber distribution hub |
| <b>Product Series</b>        | FDH 3000               |

## General Specifications

|  |                       |
|--|-----------------------|
| <b>Access</b>                                  | Front                 |
| <b>Cable Type</b>                              | Pigtails - Loose Tube |
| <b>Color</b>                                   | Putty white           |
| <b>Distribution Cables, quantity</b>           | 24                    |
| <b>Distribution Ports, quantity</b>            | 288                   |
| <b>Fibers per Distribution Cable, quantity</b> | 12                    |
| <b>Fibers per Feeder Cable, quantity</b>       | 24                    |
| <b>Interface, Input</b>                        | SC                    |
| <b>Interface Feature, Input</b>                | APC                   |
| <b>Mounting</b>                                | Pad                   |
| <b>Splitter Slots, quantity</b>                | 12                    |

## Dimensions

|                       |                  |
|-----------------------|------------------|
| <b>Height</b>         | 914.4 mm   36 in |
| <b>Width</b>          | 685.8 mm   27 in |
| <b>Depth</b>          | 457.2 mm   18 in |
| <b>Cable Length</b>   | 30.48 m   100 ft |
| <b>Enclosure Size</b> | Small            |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

# FD3-AE288J00U20P2

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

