FD3-AG360J2AJDBP2



FDH 3000 Fiber Distribution Medium Cabinet, 360F, SC/APC, no splitters, dielectric loose tube, 100 ft, 24F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

FDH 3000 **Product Series**

General Specifications

Access Front

Dielectric - Loose Tube **Cable Type**

SC

Color Putty white

3 **Distribution Cables, quantity** 432 **Distribution Ports, quantity**

Fibers per Feeder Cable, quantity 24

Interface, Input Interface Feature, Input APC

Mounting Pad

Split Ratio Symmetrical

Splitter Slots, quantity 24

1 x 32 **Splitter Type**

Splitter, quantity 2

Dimensions

Height 1,066.8 mm | 42 in Width 685.8 mm | 27 in 457.2 mm | 18 in **Depth Cable Length** 30.48 m | 100 ft

Enclosure Size Medium

Material Specifications

COMMSCOPE®

FD3-AG360J2AJDBP2

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

