## FD3-AG432J00JABP4



FDH 3000 Fiber Distribution Medium Cabinet, 432F, SC/APC, no splitters, dielectric loose tube, 100 ft, 48F

### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front

Cable TypeDielectric - Loose Tube

**Color** Putty white

**Distribution Cables, quantity** 6

**Distribution Ports, quantity** 432

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

Splitter Slots, quantity 24

### Dimensions

 Height
 1,066.8 mm | 42 in

 Width
 685.8 mm | 27 in

 Depth
 457.2 mm | 18 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Medium

Material Specifications

**Finish** Powder coated

Material Type Aluminum

COMMSC PE°

# FD3-AG432J00JABP4

## **Environmental Specifications**

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

