

FD3-PA096J1AU4320



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, 32-splitter module, stranded pigtails, 96 splice cap., 12 F feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | North America |
| Product Type | Hub in a pedestal |
| Product Series | FDH 3000 |

General Specifications

| | |
|--|---------------------|
| Access | Front Rear |
| Cable Type | Pigtails - Stranded |
| Color | Green |
| Distribution Ports, quantity | 96 |
| Fibers per Feeder Cable, quantity | 12 |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Mounting | Pedestal |
| Splice Tray Included, quantity | 4 |
| Splice Tray Type Included | 24-way, heat shrink |
| Splicing Capacity, maximum | 96 |
| Split Ratio | Symmetrical |
| Splitter Slots, quantity | 6 |
| Splitter Type | 1 x 32 |
| Splitter, quantity | 1 |

Dimensions

| | |
|---------------|----------------|
| Height | 889 mm 35 in |
|---------------|----------------|

FD3-PA096J1AU4320

| | |
|-----------------------|--------------------|
| Width | 292.1 mm 11.5 in |
| Depth | 368.3 mm 14.5 in |
| Enclosure Size | Small |

Material Specifications

| | |
|----------------------|----------------|
| Material Type | Molded plastic |
|----------------------|----------------|

Environmental Specifications

| | |
|----------------------------|--------------|
| Environmental Space | Above ground |
|----------------------------|--------------|

Packaging and Weights

| | |
|---------------------------|------------------|
| Included | Cable clamps (3) |
| Packaging quantity | 1 |
| Packaging Type | Pallet |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

