FD3-PA132J00U3420



FDH 3000 Fiber Distribution Hub in a Pedestal, 132F, SC/APC, nosplitters loaded stranded pigtails, 132 splice capacity, 12F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability

North America

Product Type

Hub in a pedestal

Product Series FDH 3000

General Specifications

Access Front | Rear

Cable Type Pigtails - Stranded

ColorGreenDistribution Ports, quantity132Fibers per Feeder Cable, quantity12Interface, InputSC

Interface Feature, Input APC

Mounting Pedestal

Splice Tray Included, quantity 3

Splice Tray Type Included 48-way, heat shrink

Splicing Capacity, maximum 132
Splitter Slots, quantity 6

Dimensions

 Height
 889 mm | 35 in

 Width
 292.1 mm | 11.5 in

 Depth
 368.3 mm | 14.5 in

Enclosure Size Small



FD3-PA132J00U3420

Material Specifications

Material Type Molded plastic

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Included Cable clamps (4)

Packaging quantity 1

Packaging Type Pallet