

760236119 | DM12iP-24LC-WB-ULL

G2 ULL Multimode OM5 MPO-12 Distribution Module, 2x12F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL

General Specifications

Adapters, quantity, front	12
Adapters, quantity, rear	2
Color, front	Lime green
Color, rear	Lime green
Data Module Type	G2
Intelligence Type	iPatch® ready
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	MPO Unpinned
Interface Feature, rear	Key up
Shuttered	No
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	24.64 mm 0.97 in
Width	94 mm 3.701 in
Depth	113.28 mm 4.46 in

Optical Specifications

Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.35 dB

Environmental Specifications

Qualification Standards	TIA/EIA-568-C.3
Safety Standard	cUL US 1863

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)