

G2 ULL Multimode OM5 MPO-24 Distribution Module, 1x24F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	SYSTIMAX ULL

## General Specifications

<b>Adapters, quantity, front</b>	12
<b>Adapters, quantity, rear</b>	1
<b>Color, front</b>	Lime green
<b>Color, rear</b>	Lime green
<b>Data Module Type</b>	G2
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	LC
<b>Interface Feature, front</b>	Standard
<b>Interface, rear</b>	MPO Unpinned
<b>Interface Feature, rear</b>	Key up
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	24.64 mm   0.97 in
<b>Width</b>	94 mm   3.701 in
<b>Depth</b>	113.28 mm   4.46 in

## Optical Specifications

<b>Fiber Type</b>	OM5, LazrSPEED® wideband
<b>Insertion Loss Change, temperature</b>	0.3 dB
<b>Insertion Loss, maximum</b>	0.35 dB

## Environmental Specifications

<b>Qualification Standards</b>	TIA/EIA-568-C.3
<b>Safety Standard</b>	cUL US 1863

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## \* Footnotes

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)