

760237221 | CM12-4X6-WB-ULL



G2 ULL 4x6 Multimode OM5 WideBand Conversion Module, (4) MPO-12 unpinned ports rear, (6) MPO-8 pinned front

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTEMAX ULL

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	4
Color, front	Lime green
Color, rear	Lime green
Data Module Type	Fiber Conversion Module
Interface, front	MPO
Interface Feature, front	Standard
Interface, rear	MPO
Interface Feature, rear	Key up Unpinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	48
Total Ports, quantity, front	6

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in

760237221 | CM12-4X6-WB-ULL

Depth 117.35 mm | 4.62 in

Optical Specifications

Fiber Mode Multimode
Fiber Type OM5, LazrSPEED® wideband
Insertion Loss, maximum 0.4 dB

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant

