

# 760237958 | EHD08-DM-24LC-LS-B-ULL



EHD ULL Multimode OM4 MPO-8 distribution module, 24LC to 3x8f MPOs unpinned, dust plugs

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber module  |
| <b>Product Brand</b>         | SYSTIMAX ULL  |
| <b>Product Series</b>        | EHD   |

## General Specifications

|                                |                            |
|--------------------------------|----------------------------|
| <b>Functionality</b>           | Breakout                   |
| <b>Color, front</b>            | Aqua                       |
| <b>Color, rear</b>             | Gray                       |
| <b>Interface, front</b>        | LC/UPC                     |
| <b>Interface, rear</b>         | MPO                        |
| <b>Interface Feature, rear</b> | Key up/up   MPO Non-Pinned |
| <b>Polarity</b>                | Method B Enhanced (ULL)    |
| <b>Shuttered</b>               | No                         |
| <b>Total Fibers, quantity</b>  | 24                         |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 12.45 mm   0.49 in  |
| <b>Width</b>  | 169.67 mm   6.68 in |
| <b>Depth</b>  | 115.32 mm   4.54 in |

## Optical Specifications

|                   |           |
|-------------------|-----------|
| <b>Fiber Mode</b> | Multimode |
|-------------------|-----------|

# 760237958 | EHD08-DM-24LC-LS-B-ULL

---

**Fiber Type** OM4, LazrSPEED® 550  
**Insertion Loss, maximum** 0.35 dB

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D  
**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 0.136 kg | 0.3 lb

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

