

CU4756-000 | OCM1-SA31200S2



OCM1 LGX Style Fiber Optic Splitter Module, FBT, three 1x2 Splitters, singlemode, SC/APC, 50/50 split ratio

Product Classification

Regional Availability	EMEA Latin America North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Fused biconic tapered
Access	Front
Application	For use with LGX panels
Circuits, quantity	3
Distribution Type	1 x 2 splitter
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	3

Dimensions

Height	129.54 mm 5.1 in
Width	27.94 mm 1.1 in
Depth	127 mm 5 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Packaging Type

Box | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

