CZ8312-000 | OCM6-SP11GNS2-61CB1



OCM6 Fiber Optic Splitter Module, Planar, one 1x16 Splitter, singlemode, SC/APC output only, symmetrical split ratio, butt style, 61 cm pigtails

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM	
Functionality	Splitting	
Technology Type	Planar lightwave circuit (PLC)	
Application	For use with BUDI wall boxes	
Circuits, quantity	1	
Distribution Type	1 x 16 splitter	
Interface, Input	Stub tail	
Interface, Output	SC/APC	
Split Ratio	Symmetrical	
Splitter, quantity	1	
Dimensions		
Height	130 mm 5.118 in	
Width	49.8 mm 1.961 in	
Depth	16.5 mm 0.65 in	
Pigtail Length, Input	0.61 m 2.001 ft	
Pigtail Length, Output	0.61 m 2.001 ft	
Pigtail Diameter	1.8 mm 0.071 in	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



CZ8312-000 | OCM6-SP11GNS2-61CB1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

