

EG6568-000 | OCM6-SP12GL2-45DB1



OCM6 Fiber Optic Splitter Module, Planar, one 2x16 Splitter, singlemode, LC/APC, symmetrical split ratio, butt style, 4.5 m pigtails

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use with BUDI wall boxes
Circuits, quantity	1
Distribution Type	2 x 16 splitter
Interface, Input	LC/APC
Interface, Output	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	4.5 m 14.764 ft
Pigtail Length, Output	4.5 m 14.764 ft
Pigtail Diameter	1.8 mm 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

