

EH0787-000 | OCM1-SP11800L2



OCM1 LGX Style Fiber Optic Splitter Module, Planar, one 1x8 Splitter, singlemode, LC/APC, symmetrical split ratio

Product Classification

Regional Availability	EMEA Latin America North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Access	Front
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	1 x 8 splitter
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	129.54 mm 5.1 in
Width	27.94 mm 1.1 in
Depth	127 mm 5 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

