


# FMT-MS27U7U2600B00

---



FMT MicroVAM Fiber Optic Splitter Module, two 1x2 splitters, singlemode, SC/UPC, 80/20 split ratio

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	FMT

## General Specifications

<b>Device Type</b>	Micro VAM
<b>Functionality</b>	Splitting
<b>Access</b>	Front
<b>Application</b>	For use with FMT panels   For use with NGF frames
<b>Circuits, quantity</b>	2
<b>Distribution Type</b>	1 x 2 splitter
<b>Interface, front</b>	SC/UPC
<b>Interface, Input</b>	SC/UPC
<b>Interface, Output</b>	SC/UPC
<b>Split Ratio</b>	80/20
<b>Splitter, quantity</b>	2

## Dimensions

<b>Height</b>	71.88 mm   2.83 in
<b>Width</b>	17.27 mm   0.68 in
<b>Depth</b>	177.8 mm   7 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

# FMT-MS27U7U2600B00

---

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

