# 760082487 | RK3-52A



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** 2 post rack

#### General Specifications

**Color** Black

**Rack Type** EIA 19 in

Rack Units 52

**Rail Mounting Hole** #12-24

#### Dimensions

**Height** 2,438.4 mm | 96 in

Channel Width 76.2 mm | 3 in

**Width** 518.16 mm | 20.4 in

**Depth** 381 mm | 15 in

**Dimensional Standards** EIA-310-E

## Material Specifications

**Finish** Powder-coated, textured

Material Type Aluminum

### Mechanical Specifications

**Static Load Rating** 453.6 kg | 1,000.016 lb

### Packaging and Weights

Included Forty #12-24 x 1/2 in mounting screws | Instruction sheet | Twelve 3/8 in split lock

washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base

Page 1 of 2

# 760082487 | RK3-52A

angles | Two extruded top angles | Two vertical rack rails

Packaging quantity

Packaging Type Flat packed

**Weight, net** 15.88 kg | 35.009 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



