



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	52
Rail Mounting Hole	#12-24

Dimensions

Height	2,438.4 mm 96 in
Channel Width	76.2 mm 3 in
Width	518.16 mm 20.4 in
Depth	381 mm 15 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

Mechanical Specifications

Static Load Rating	453.6 kg 1,000.016 lb
---------------------------	-------------------------

Packaging and Weights

Included	Forty #12-24 x 1/2 in mounting screws Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8-16 UNC x 1 in hex head bolts Twelve 3/8-16 hex nuts Two extruded base
-----------------	---

760082487 | RK3-52A

angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1
Packaging Type Flat packed
Weight, net 15.88 kg | 35.009 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

