

760082594 | RK4P52-36S



Equipment Rack, 4-Post, 36 in (914 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

OBSOLETE

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type 4 post rack

General Specifications

Color Black

Rack Type EIA 19 in

Rack Units 52

Rail Mounting Hole 3/8 in

Dimensions

Height 2,438.4 mm | 96 in

Channel Width 76.2 mm | 3 in

Width 518.16 mm | 20.4 in

Depth 1,219.2 mm | 48 in

Dimensional Standards EIA-310-E

Material Specifications

Finish Powder-coated, textured

Material Type Steel

Mechanical Specifications

760082594 | RK4P52-36S

Static Load Rating 907.2 kg | 2,000.031 lb

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Base pan | Forty #12-24 x 1/2 in mounting screws | Forty M6 cage nuts | Four vertical rack rails | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

Packaging quantity 1

Packaging Type Flat packed

Weight, net 56.25 kg | 124.01 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

