

760092007 | RK3-45AM



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) M6 Tapped Rails, Black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760090118
RK3-45S

Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | 2 post rack |

General Specifications

| | |
|---------------------------|-----------|
| Color | Black |
| Rack Type | EIA 19 in |
| Rack Units | 45 |
| Rail Mounting Hole | M6 |

Dimensions

| | |
|------------------------------|---------------------|
| Height | 2,133.6 mm 84 in |
| Channel Width | 76.2 mm 3 in |
| Width | 518.16 mm 20.4 in |
| Depth | 381 mm 15 in |
| Dimensional Standards | EIA-310-E |

Material Specifications

| | |
|----------------------|-------------------------|
| Finish | Powder-coated, textured |
| Material Type | Aluminum |

760092007 | RK3-45AM

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Weight, net 12.7 kg | 27.999 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

