

# 760139121 | RK6-58S



Rack, 2-Post, (58U), 6 in (152 mm) Channel x 9 ft (2743 mm) H x 19 in (482.6 mm) W, steel, 3/8 square punch, black

## OBSOLETE

This product was discontinued on: November 30, 2018

### Replaced By:

760090142  
RK6-52S

Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	58
<b>Rail Mounting Hole</b>	3/8 in

## Dimensions

<b>Height</b>	2,743.2 mm   108 in
<b>Channel Width</b>	152.4 mm   6 in
<b>Width</b>	515.62 mm   20.3 in
<b>Depth</b>	457.2 mm   18 in
<b>Dimensional Standards</b>	EIA-310-D

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Steel

# 760139121 | RK6-58S

---

## Mechanical Specifications

**Static Load Rating** 453.6 kg | 1,000.016 lb

## Packaging and Weights

**Included** Forty M6 cage nuts | Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

**Packaging quantity** 1

**Packaging Type** Flat packed

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

