

# CC5206-000 | FIST-GPS2-J-AAL1-4

---

FIST-GPS2 Fiber Termination/Splice Panel, LC/UPC, 2RU, 19 in, gray

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-GPS2

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in FIST-GR3-style frames only
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Interface, front</b>	LC/UPC
<b>Rack Type</b>	EIA 19 in   ETSI 600 mm
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +45 °C (+23 °F to +113 °F)
<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)

# CC5206-000 | FIST-GPS2-J-AAL1-4

---

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

