

# CK4386-000 | FIST-GPS3-K-1

---

FIST-GPS3 Fiber Panel for holding up to 2 GPST Patch/Splice Trays, unloaded, 1RU, 19 in, gray

## Product Classification

|                              |                          |
|------------------------------|--------------------------|
| <b>Regional Availability</b> | EMEA                     |
| <b>Portfolio</b>             | CommScope®               |
| <b>Product Type</b>          | Fiber patch/splice panel |
| <b>Product Brand</b>         | FIST®                    |
| <b>Product Series</b>        | FIST-GPS3                |

## General Specifications

|                             |                                     |
|-----------------------------|-------------------------------------|
| <b>Functionality</b>        | Patching   Splicing                 |
| <b>Application</b>          | Used in FIST-GR3F-style frames only |
| <b>Color</b>                | Gray                                |
| <b>Color, front</b>         | Gray                                |
| <b>Growth Configuration</b> | Unloaded                            |
| <b>Interface, front</b>     | Unloaded                            |
| <b>Rack Type</b>            | EIA 19 in                           |
| <b>Rack Units</b>           | 1                                   |
| <b>Shelf Movement</b>       | Sliding                             |

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 44 mm   1.732 in   |
| <b>Width</b>  | 482 mm   18.976 in |
| <b>Depth</b>  | 280 mm   11.024 in |

## Material Specifications

|                      |                  |
|----------------------|------------------|
| <b>Finish</b>        | Powder coated    |
| <b>Material Type</b> | Galvanized steel |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -5 °C to +45 °C (+23 °F to +113 °F)  |
| <b>Storage Temperature</b>   | -30 °C to +60 °C (-22 °F to +140 °F) |

# CK4386-000 | FIST-GPS3-K-1

---

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

