

CW0093-000 | OCFPS1U-P113200S1



OCFPS Fiber Optic Splitter Panel, one 1x32, symmetrical, planar, singlemode, SC/UPC, 1U, 19 in, gray

OBSOLETE

This product was discontinued on: September 18, 2023

Replaced By:

1RU-SP4132001 1RU panel, 1X32 split ratio, 1 splitter, SC/UPC connectors
1RU SPLTR PNL 1X32 UPC/SC

Product Classification

| | |
|------------------------------|----------------------|
| Regional Availability | North America |
| Portfolio | CommScope® |
| Product Type | Splitter patch panel |
| Product Series | OCFPS |

General Specifications

| | |
|---------------------------|--------------------------------|
| Device Type | Patch panel |
| Functionality | Splitting |
| Technology Type | Planar lightwave circuit (PLC) |
| Circuits, quantity | 1 |
| Distribution Type | 1 x 32 splitter |
| Interface, front | SC/UPC |
| Split Ratio | Symmetrical |
| Splitter, quantity | 1 |

Dimensions

| | |
|---------------|--------------------|
| Height | 43.5 mm 1.713 in |
| Width | 440 mm 17.323 in |
| Depth | 210 mm 8.268 in |

Ordering Tree

OCFPS 1U - X X X X X X

Shelf Type

| | |
|-----|--------------------|
| 1HU | 1 RU High 19" wide |
|-----|--------------------|

Splitter Grade

| | |
|---|---------------------------|
| A | FBT type |
| P | Planar grade P |
| O | Planar grade O (low loss) |

Number of Splitters

| | Shelf type 1 | |
|--------|--------------|-----------|
| | Grade A | Grade P/O |
| 1 x 2 | 16 | - |
| 2 x 2 | 16 | - |
| 1 x 4 | - | 6 |
| 2 x 4 | - | 6 |
| 1 x 8 | - | 6 |
| 2 x 8 | - | 6 |
| 1 x 16 | - | 2 |
| 2 x 16 | - | 2 |
| 1 x 32 | - | 2 |
| 2 x 32 | - | 1 |
| 1 x 64 | - | 1 |
| 2 x 64 | - | 1 |

Connector Type

| | |
|----|-----------|
| S1 | SC/UPC |
| S2 | SC/APC 8° |
| S3 | SC/APC 9° |
| L1 | LC/UPC |
| L2 | LC/APC |

Split Ratio

| | |
|----|-------------|
| 00 | Symmetrical |
|----|-------------|

Number of Output Ports

| | |
|----|-------------------|
| 02 | ... x 2 splitter |
| 04 | ... x 4 splitter |
| 08 | ... x 8 splitter |
| 16 | ... x 16 splitter |
| 32 | ... x 32 splitter |
| 64 | ... x 64 splitter |

Number of Input Ports

| | |
|---|-----------------|
| 1 | 1 x ...splitter |
| 2 | 2 x ...splitter |

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
 REACH-SVHC
 ROHS
 UK-ROHS

Classification

Below maximum concentration value
 Compliant as per SVHC revision on www.commscope.com/ProductCompliance
 Compliant
 Compliant

