



FACT® Fiber Optic Termination Panel, 96-port, LC/UPC, grade C

- Lightweight, compact and fully configurable with a variety of adapters, splicing and passive optical components
- Cable attachment bracket kits allow secure mounting of different cable types and patch cords to the sides of the FACT panel
- Each FACT panel unit -offering 48 LC connections- can be deployed individually or combined into high-density panels
- Designed for use with the FIST-GR3 optical distribution frame for holding up to 56 FACT panel units

OBSOLETE

This product was discontinued on: July 31, 2018

Replaced By:

760239982
FACT-2EPATL1

FACT® Fiber Optic Patch Panel, gray, 2E high, 96-port, singlemode, holding 4 hinged trays loaded with LC/UPC adapters

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Patching
Application	Compatible with FIST-GR3-style frames
Color	Gray
Color, front	Gray
Interface, front	LC
Interface Feature, front	Standard
Patch Cord Routing	Left sided Right sided
Rack Type	EIA 19 in ETSI 600 mm
Rack Units	1.4

EG9883-000 | FACT-GPS-096L1AA-ONN

Shelf Movement Sliding

Total Ports, quantity 96

Dimensions

Height 61.9 mm | 2.437 in

Width 524 mm | 20.63 in

Depth 283 mm | 11.142 in

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -20 °C to +85 °C (-4 °F to +176 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

