

F59479-000 | FOMS-STO-1U-NR

FOMS-FPS Fiber Storage Panel, 1U, 19 in, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber storage panel
Product Series	FOMS-FPS

General Specifications

Functionality	Slack storage
Color	Gray
Color, front	Gray
Growth Configuration	Unloaded
Interface, front	Unloaded
Patching Capacity, maximum	0
Rack Type	EIA 19 in EIA 23 in ETSI 600 mm
Rack Units	1
Shelf Movement	Hinged
Splicing Capacity, maximum	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Material Specifications

Material Type	Ethylene-propylene (EP) Polyethylene terephthalate (PET)
----------------------	--

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

F59479-000 | FOMS-STO-1U-NR

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

