

DLX® Fiber Indexing Terminal, 1x4 Splitter, 4 Forward Ports, 1 Reverse Port, Dielectric Flat Loose Tube Cable, 200 Feet

Product Classification

Regional Availability North America

Product Type Access terminal, indexed with splitter

Product Brand DLX®
Product Series NDX

General Specifications

Cable TypeDielectric - Flat - Loose Tube

Cable, quantity

Distribution Type 1 x 4 splitter

Enclosure Color Black

Forward Port Type Hardened mini-size (DLX) adapter

Forward Port, quantity 4

 Mounting
 Handhole
 | Pedestal
 | Pole

 Port Type
 Hardened multi-fiber (HMFOC) jack

Port, quantity

Reverse Port TypeHardened mini-size DLX

Reverse Port, quantity 1
Splitter, quantity 1

Stub Type Hardened multi-fiber (HMFOC) plug

Dimensions

 Height
 297.8 mm | 11.724 in

 Width
 130.3 mm | 5.13 in

 Depth
 90.4 mm | 3.559 in

Page 1 of 5




Cable Length, stub

200 ft (60 m)


Cable Outer Diameter

4.5 x 8.1 mm (0.18 x 0.32 in)

Dimension Drawing



Ordering Tree



Material Specifications

Enclosure Material Type	Gasketed hardened plastic
-------------------------	---------------------------

Optical Specifications

Operating Wavelength Range 1260 – 1635 nm

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Splitter, maximum7.1 dBAttenuation Terminal Connectors, maximum0.45 dBDirectivity, minimum60 dB

Uniformity, maximum 0.8 dB

Insertion Loss, Splitter, typical 6.7 dB

COMMSCOPE®

Insertion Loss, Stub Connector, maximum0.45 dBInsertion Loss, Stub Connector, typical0.16 dBInsertion Loss, Terminal Connector, typical0.16 dBReturn Loss, Connector, minimum65 dBReturn Loss, Single Ports, minimum55 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground | Buried

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP68 + 2 m waterhead | NEMA, Type 6 + 10 ft

waterhead | Telcordia GR-3120-CORE | Telcordia GR-326-

CORE | Telcordia GR-771-CORE

UV Resistance UV stabilized

Packaging and Weights

Included Enclosure (1) | Optical splitter (1) | Universal mounting bracket (1)

Packaging quantity 1

Packaging TypeBox| CartonWeight, without cable1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

MST-LIMB-MINI - DLX® Mini-MST, Fiber Optic Universal Mounting

Bracket



