# 130884-000 | XAGA-550-160/42-500



XAGA® 550 Copper Closure, unpressurized, heat shrink, 500 mm sheath opening, 160 mm splice bundle diameter

- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

#### **OBSOLETE**

This product was discontinued on: June 30, 2022

### **Product Classification**

Regional Availability EMEA

Product Type Unpressurized heat shrink closure

Product Brand XAGA®
Product Series XAGA 550

### General Specifications

**Application** For use with Polyethylene and metal jacketed cables

**Branch-off Clip**To be ordered seperately

Cable Capacity, maximum 3

 Cable Sealing Type
 Hotmelt adhesive

Color In-line Black

 Mounting
 Duct
 | Manhole

 Splice Protection Type
 Metal canister


### **Dimensions**

Single Cable Diameter, minimum42 mm | 1.654 inSplice Bundle Diameter, maximum160 mm | 6.299 inSheath Opening, nominal500 mm | 19.685 in

## Dimension Drawing

Page 1 of 2

# 130884-000 | XAGA-550-160/42-500



## Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

### **Environmental Specifications**

Environmental Space Aerial | Below ground | Buried

## Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible

stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity

wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



