


XAGA® 550L Copper Closure, unpressurized, heat shrink, 17 inch sheath opening, 1.7 inch splice bundle diameter



- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America North America
Product Type	Unpressurized heat shrink closure
Product Brand	XAGA®
Product Series	XAGA 550L

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	3
Cable Sealing Type	Hotmelt adhesive
Closure Style	In-line
Color	Black
Mounting	Duct Manhole
Splice Protection Type	Metal canister

Dimensions

Single Cable Diameter, minimum	8.89 mm 0.35 in
Splice Bundle Diameter, maximum	43.18 mm 1.7 in
Sheath Opening, nominal	431.8 mm 17 in

Dimension Drawing



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

