423303-000 | XAGA550L-A4-170/35-M463



XAGA® 550L Copper Closure, unpressurized, heat shrink, 37 inch sheath opening, 1.7 inch splice bundle diameter

- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional AvailabilityLatin America | North AmericaProduct TypeUnpressurized heat shrink closure

Product Brand XAGA®

Product Series XAGA 550L

General Specifications

Application For use with Polyethylene and metal jacketed cables

Branch-off ClipTo be ordered seperately

Cable Capacity, maximum 3

Cable Sealing Type Hotmelt adhesive

Color In-line Black

Mounting

Duct | Manhole

Splice Protection Type

Metal canister

Dimensions


Single Cable Diameter, minimum8.89 mm | 0.35 inSplice Bundle Diameter, maximum43.18 mm | 1.7 inSheath Opening, nominal939.8 mm | 37 in

Dimension Drawing

Page 1 of 2



423303-000 | XAGA550L-A4-170/35-M463



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible

stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity

wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



COMMSCOPE®