

# 760237942 | EHD-SP-24LC-SMR-AS-ULL



EHD ULL 24f LC UPC ribbon splice cassette Singlemode, includes 2, FST-ACC006 mass fusion splice sleeves

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Brand</b>	SYSTIMAX ULL
<b>Product Series</b>	EHD

## General Specifications

<b>Adapters, quantity, front</b>	24
<b>Adapters, quantity, rear</b>	0
<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Ribbon pigtail
<b>Polarity</b>	Method A   Pairs, straight
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	12.446 mm   0.49 in
<b>Width</b>	169.672 mm   6.68 in
<b>Depth</b>	163.83 mm   6.45 in

## Optical Specifications

<b>Fiber Type</b>	G.657.A2
-------------------	----------

## Environmental Specifications

<b>Safety Standard</b>	cUL US 1863
------------------------	-------------

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.454 kg   1 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## Included Products

FST-ACC006	- Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack
------------	-----------------------------------------------------------------